

Trojan Type 'M' Self Contained Portable Power Pack

ATEX  II 2G Ex h IIC T5 Gb
II 2D Ex h IIIC T100°C Db

Simple to operate:-

- 1/ Connect air supply.
 - 2/ Connect liquid supply if no reservoir.
 - 3/ Connect to test specimen.
 - 4/ Perform Pressure Test.
 - 5/ Release pressure.
- End of Test.




(Shown with optional Reservoir and Carrying Handle.)

Whether intended to be used as a mobile unit or installed in a permanent position the **Portable Power Pack** has been developed to provide a ready to use pressure testing rig.

Suitable for use with oil or water and available with or without a liquid reservoir the **Portable Power Pack** has the following features:-

- 1/ Output pressures up to 3,040 depending on the model of **Trojan Type 'M'** pump fitted.
- 2/ Air inlet on/off ball valve.
- 3/ Air inlet combined filter and pressure regulator.
- 4/ Air Pressure Gauge
- 5/ Liquid inlet strainer.
- 6/ Outlet pressure gauge.
- 7/ Outlet pressure release valve. (piped back to reservoir when fitted).
- 8/ Sturdy stainless steel frame.
- 9/ Optional stainless steel reservoir (26 litres) with drain tap, filler cap, strainer and level sight glass.
- 10/ Optional carrying handles with reservoir.

70cm (x 25cm DEEP)



Available from:- Hydraulic Pneumatic Services Ltd, Unit 17, King St. Industrial Estate, Middlewich, Cheshire, CW10 9LF.(UK) Tel:-+44 (0)1606 835725 Web site www.trojanpumps.com .
Email: enquiries@pressure-pumps.co.uk